

# YA4CA8

by Burndy  
Catalog ID: YA4CA8

4 AL 1-HOLE



\* Representative image

## Product Details

### General

Connector Type	Terminal
Feature - Barrel Type	Standard
Material	Aluminum
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
UPC	781810568774
UPC 12 Digit	7818105687744

### Dimensions

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Certifications and Compliance

Certification - CSA Approved	Yes
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	6000
-----------------------	------

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)