

YA4CL2TC14E2

by Burndy
Catalog ID: YA4CL2TC14E2

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 4 AWG, 1/4" Stud, 3/4" Stud Hole Spacing, Short Barrel, Tin - Electro Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, Die Index: 8, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Wire Strip Length: 7/8 IN, Tongue Angle: Straight, Color Code: Gray, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W4CVT Die, (1), Hydraulic: BCT500HS, Y500CTHS Tool, X4CRT Die, (1), Y35, Y39, Y750, PAT750 Tool, U4CRT Die, (1), Y46 Tool, U4CRT Die With PUADP-1 Adapter, (1), Conductor Type: Commercial Stranded Copper, Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11, MRC840 Tool, (1), Y1MRTC Tool, (2)



Product Details

General

Application	For Code Conductor
Color Code	Gray
Connector Type	Terminal
Die Index	8 ; 346
Feature - Barrel Style	<ul style="list-style-type: none"> Chamfered Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin Plating
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810018224
UPC 12 Digit	7818100182244

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	1.39 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - L Length Overall mm	63 mm
Dimension - Length Overall inch	2.49 in

Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.34 in
Dimension - Pad Width inch	0.5 in
Dimension - Strip Length inch	7/8 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.33
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	#4 AWG
Conductor - Copper Str Navy Size	40 (19) Navy
Conductor - Copper Str Navy Size Range	40 (19) Navy
Conductor - Copper Str Size	#4 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL 486A-486B
Standards - Industry Standards Met	UL 486A-486B
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)