



## YA6C2

by Burndy  
Catalog ID: YA6C2

Prop 65 Notice

Uninsul Cu Comp Terminal Code Cond, Bvl Entry, W/O/InspWindow, #6 Str, 600 V-35 kV, 1/4" Stud, Lng bbl, Tin Plated, Blue.

Tongue Angle: Straight, Conductor Type: Stranded Copper

## Product Details

### General

Application	For Aluminum & Copper Conductors
Color Code	Blue
Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Straight
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Tin Plated
UPC	781810501801
UPC 12 Digit	7818105018011

### Dimensions

Dimension - B Length inch	1.12
Dimension - Bolt Hole Size inch	0.281
Dimension - Hole Size inch	0.281
Dimension - Length Overall inch	2.5
Dimension - N inch	0.25
Dimension - Outside Diameter inch	0.3
Dimension - Pad Width inch	0.41
Dimension - Strip Length inch	1.18 in
Dimension - Z inch	0.41
Physical Attribute - Tongue Angle	Straight

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600

Voltage - Maximum	35000
-------------------	-------

## Conductor Related

Conductor - Copper Solid Size	6 AWG
Conductor - Copper Str Size	6 AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)