

# YAD1410M

by Burndy  
Catalog ID: YAD1410M

Prop 65 Notice

Uninsulated CU Compression Ring Terminal, Cable Size: 20 - 14 AWG,  
Stud Size: #8 - #10, 0.96 in L, 0.46 in W, Tin Plated, Reel



## Product Details

### General

Connector Type	Terminal
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810028186
UPC 12 Digit	7818100281866

### Dimensions

Dimension - Hole Size fraction	1/5
Dimension - Hole Size inch	0.20 in
Dimension - Length Overall inch	0.77 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.33 in

### Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

### Conductor Related

Conductor - Copper Str Size Range	20 AWG-14 AWG
-----------------------------------	---------------

Conductor Type	CU C Str-Size
----------------	---------------

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	2000
Packaging Type	Reel

**For further technical assistance, please contact us**

### **BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

### **Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)