

YAD1414

by Burndy
Catalog ID: YAD1414

Prop 65 Notice

Uninsulated CU Compression Ring Terminal, Cable Size: 20 - 14 AWG, Stud Size: 1/4 IN, Wire Strip Length: 9/32 IN, Package: Bulk.

Features: Constructed Of Pure Electrolytic Copper: Provides Maximum Conductivity, Low Resistance And Ductility For Excellent Crimp Forming Properties, Long Brazed Seam Barrel And Deep V Groove Inner Serrations: Provides Optimum Conductivity Reliability And Holding Power After Crimping, Electro-Tin Plated: Provides Durable Long-Lasting Corrosion Resistance, Wire Range Is Clearly Marked On Terminal: Provides Easy Identification, Inspection Hole: Provides An Easy Visual Check Of Wire Insertion, Long Neck Terminal: Permits Easy Bending And Stacking Of Several Terminals On A Common Stud, Wire Strip Length: 9/32 IN, Finish: Electro-Tin Plated, Installation Tool: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: Y8MRB-1, MR20, MR8G98 Tool, Package: Bulk



Product Details

General

Application	For control wiring and other standard duty applications
Connector Type	Terminal
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Fork
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810806142
UPC 12 Digit	7818108061422

Dimensions

Dimension - Hole Size fraction	10/37
Dimension - Hole Size inch	0.27 in
Dimension - L Length Overall mm	24 mm
Dimension - Length Overall inch	0.96 in
Dimension - Pad Width inch	0.45 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.44 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Type	CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)