

YAD26M10E38

by Burndy
Catalog ID: YAD26M10E38

Prop 65 Notice

Non Insulated Brazed Barrel Copper Terminal, 2/0 AWG Str.Cu Code & Flex (50-70)mm, 3/8", 1.59 in L, .91 in W, Tin Plated.

Features:Terminals utilize a brazed seam, Provide excellent high conductivity connections, Electro-tin plated for durable long lasting corrosion resistance, Vibration resistance and tensile strength is well within the limits of commercial specificatoinis



Product Details

General

Application	The YAD uninsulated OEM lug terminal is constructed of electrolytic copper
Connector Type	Terminal
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810549438
UPC 12 Digit	7818105494388

Dimensions

Dimension - B Length inch	0.71 in
Dimension - Hole Size inch	0.41 in
Dimension - L Length Overall mm	49 mm
Dimension - Length Overall inch	1.93 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Pad Width inch	0.91 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	3/8

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Str Size	2/0 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Str-Size • CU C Flex-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Carton Quantity	500 EA
Minimum Pack Quantity	50

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)