



YAG38LTC12FX

by Burndy
Catalog ID: YAG38LTC12FX

Prop 65 Notice

Copper Compression Terminal

Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	L99
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810194263
UPC 12 Digit	7818101942633

Dimensions

Dimension - B Length fraction	1-7/16 in
Dimension - B Length inch	1.45 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Bolt Size fraction	1/2
Dimension - Hole Size inch	0.53 in
Dimension - Hole Size mm	13 mm
Dimension - L Length Overall mm	88 mm
Dimension - Length Overall inch	3.46 in
Dimension - N inch	0.53 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.84 in
Dimension - Strip Length inch	1-7/16 in
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.55 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	535 kcmil; (1325/24)
Conductor - Copper Flex G Size	550 kcmil
Conductor - Copper Flex H Size	550 kcmil
Conductor - Copper Flex I Size	550 kcmil
Conductor - Copper Flex K Size	550 kcmil
Conductor - Copper Flex M Size	500 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)