



YAK34A2G2

by Burndy
Catalog ID: YAK34A2G2

Prop 65 Notice

Cast Al Straight Stacking Lug, 2-NEMA Holes, 500 kcmil Al, 500 kcmil Al Compressed, 0.56" Hole Dia.

Features: Compression Terminal, Conductor Type: Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U317, U705 Die, Y45 Tool, U317, U705 Die With PT-6515 Adapter, Y46 Tool, U317, U705 Die With PUADP-1 Adapter, Die Index: 317 Or 705, Tongue Angle: Straight

Product Details

General

Application	For Aluminum
Connector Type	Terminal
Die Index	317;705
Feature - Barrel Style	Chamfered
Material	Aluminum Alloy
Physical Attribute - Number of Crimps Required	2
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YAK-A-2G, Stacking Lug
UPC	781810802281
UPC 12 Digit	7818108022811

Dimensions

Dimension - B Length inch	2.41 in
Dimension - Bolt Hole Size inch	0.50 in
Dimension - D inch	3.06 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	197 mm
Dimension - Length Overall inch	7.75 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.25 in
Dimension - Pad Width inch	1.62 in
Dimension - Strip Length inch	2-1/2 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	500 kcmil
Conductor - AL Str Size Range	500 kcmil
Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	3
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)