



YAV102TC1090

by Burndy
Catalog ID: YAV102TC1090

Cu terminal, 2 Holes/W/insp W, #14-#10 STR,#12-#10 SOL, #10" stud, Tin - Electro Plated.

Two hole copper terminal, tin-electro plated

Product Details

General

Application	For Code Conductor
Connector Type	Terminal
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810022122
UPC 12 Digit	7818100221222

Dimensions

Dimension - B Length fraction	3/8 in
Dimension - B Length inch	0.38 in
Dimension - Bolt Hole Size inch	0.20 in
Dimension - D inch	1.13 in
Dimension - Height inch	0.64 in
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	34 mm

Dimension - Length Overall inch	1.33 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.21 in
Dimension - Pad Width inch	0.36 in
Dimension - Strip Length inch	7/16
Dimension - Stud Size inch	#10
Dimension - Z inch	0.26 in
Physical Attribute - Tongue Angle	90 Degree

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
Conductor - Copper Solid Size	12 AWG;11 AWG;10 AWG
Conductor - Copper Solid Size Range	12 AWG-10 AWG
Conductor - Copper Str Size	14 AWG;12 AWG;10 AWG
Conductor - Copper Str Size Range	14 AWG-10 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)