



## YAV18T5BOX

by Burndy  
Catalog ID: YAV18T5BOX

Prop 65 Notice

Uninsulated Cu Compression Terminal, Ring Tongue, #22 - #18 AN, #4- #6 stud

## Product Details

### General

Connector Type	Terminal - Ring
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810543009

### Dimensions

Dimension - B Length fraction	17/81 in
Dimension - B Length inch	0.21 in
Dimension - D inch	0.40 in
Dimension - L Length Overall mm	19 mm
Dimension - Length Overall inch	0.76 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.13 in
Dimension - Pad Width inch	0.31 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#4;#5;#6
Dimension - Z inch	0.24 in

### Conductor Related

Conductor - Copper Solid Size	22 AWG;20 AWG;18 AWG
Conductor - Copper Solid Size Range	22 AWG-18 AWG
Conductor - Copper Str Aircraft Size	AN 22;AN 20;AN 18
Conductor - Copper Str Aircraft Size Range	AN 22-AN 18
Conductor - Copper Str Navy Size	1 (1);1 (7);1 (10);1 1/2 (1);1 1/2 (7);1 1/2 (16);1 1/2 (41);2 (7)
Conductor - Copper Str Navy Size Range	1 (1)-2 (7)
Conductor - Copper Str Size	22 AWG;20 AWG;18 AWG

Conductor - Copper Str Size Range	22 AWG-18 AWG
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)