



YAV1CL3BOX

by Burndy
Catalog ID: YAV1CL3BOX

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole W/ Inspection Hole, AN-1 Flex, 1/2" Stud, Short Barrel, Tin Plated, Die index:42

Product Details

General

Connector Type	Terminal
Die Index	42
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> • DLP Copper • Tin Plating
Military Specification	MS20659
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810539903

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - D inch	0.89 in
Dimension - Hole Size mm	13 mm
Dimension - Length Overall inch	1.97 in
Dimension - N inch	0.43 in
Dimension - Outside Diameter inch	0.47 in
Dimension - Pad Width inch	0.86 in
Dimension - Strip Length inch	5/8 in
Dimension - Stud Size inch	1/2
Dimension - Z inch	0.46 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor - Copper Str Size	1
Conductor - Copper Str Size Range	1
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none">• UL467• Military Specified (Mil-Spec)
Standards - Industry Standards Met	<ul style="list-style-type: none">• UL467• Military Specified (Mil-Spec)
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)