



## YAV1CLNK

by Burndy  
Catalog ID: YAV1CLNK

Prop 65 Notice

Copper Compression Lug, Heavy Duty, Ring Tongue, 1 Hole W/ Inspection Hole, AN-1 Flex, 3/8" Stud, Short Barrel, Nickel Plated

Features: Large Size Seamless Uninsulated Compression Terminal, Double thick Tongue, With Inspection Window: Finish: Nickel Plated

## Product Details

### General

Application	For use on: Type AN aircraft cable, extra flexible conductors and commercial(code) conductors, Applications include aircraft, industrials, hospitals, electric utilities, marine, computers, and other equipment subject to vibration or requiring dependable electrical Performance
Connector Type	Terminal
Construction Material - Main	Copper tubing
Die Index	42
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Sub Brand	Terminals, HYLUG
Trade Name	HYLUG™
Type	YAV-L, Ring Tongue
UPC	781810025444

### Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - D inch	0.76 in
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	1.84 in
Dimension - N inch	0.38 in
Dimension - Outside Diameter inch	0.51 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	3/8 in

Dimension - Z inch	0.38 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper Str Aircraft Size	AN 1
Conductor - Copper Str Aircraft Size Range	AN 1
Conductor Type	<ul style="list-style-type: none"><li>• CU C Solid-Size</li><li>• CU C Str-Size</li></ul>

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)