



## YAV25L2NK

by Burndy  
Catalog ID: YAV25L2NK

Prop 65 Notice

Copper Compression Lug, Ring Tongue, 1 Hole W/ Inspection Window,  
AN-1/0 Flex, 5/16" Stud, Short Barrel, Nickel Plated

## Product Details

### General

Connector Type	Terminal
Die Index	43
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810163139

### Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.85 in
Dimension - Hole Size mm	8 mm
Dimension - Length Overall inch	2.03 in
Dimension - N inch	0.42 in
Dimension - Outside Diameter inch	0.57 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	5/16 in
Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

### Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Conductor - Copper Str Aircraft Size	AN 0
Conductor Type	<ul style="list-style-type: none"> <li>• CU C Solid-Size</li> <li>• CU C Str-Size</li> </ul>

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	100
-----------------------	-----

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)