



YAV25LNK

by Burndy
Catalog ID: YAV25LNK

Prop 65 Notice

Cu Large Size Uninsul Comp Terminal, Ring Tongue/Bvl Entry, W/InspWindow, 1/0 AWG, 3/8" Stud, Seamless bbl, Nickel Plated, 43 Index.

copper Large Size Uninsul Comp Terminal, Ring Tongue, Seamless barrel, Nickel Plated

Product Details

General

Application	For Use On Type AN Aircraft Cable, Extra Flexible Conductors And Commercial (Code) Conductors, Industrials, Hospitals, Electric Utilities, Marine, Computers, And Other Equipment Subject To Vibration Or Requiring Dependable Electrical Performance
Connector Type	Terminal
Die Index	43
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Nickel
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810085813

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.39 in
Dimension - D inch	0.85 in
Dimension - Hole Size mm	10 mm
Dimension - Length Overall inch	2.03 in
Dimension - N inch	0.42 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Stud Size inch	3/8 in

Dimension - Z inch	0.43 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN 0
Conductor - Copper Str Aircraft Size Range	AN 0
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)