



YAV25LTC10FX

by Burndy
Catalog ID: YAV25LTC10FX

Prop 65 Notice

Cu Tubing Compression Terminal, 1 Hole W/InspWindow, 1/0 AWG Class G-M, 1/0 (275/#24)DLO, 1/0 AWG Class B,C Code, 100 Navy, #10 Stud, Standard Brll

Product Details

General

Color Code	Pink
Connector Type	Terminal
Die Index	12
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810223666
UPC 12 Digit	7818102236666

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.69 in
Dimension - Bolt Hole Size inch	0.21
Dimension - Hole Size inch	0.21 in
Dimension - Hole Size mm	5 mm
Dimension - L Length Overall mm	41 mm
Dimension - Length Overall inch	1.63 in
Dimension - N inch	0.25 in
Dimension - Outside Diameter inch	0.56 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Z inch	0.27 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
--------------	-------

Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24) DLO
Conductor - Copper Flex G Size	1/0 AWG
Conductor - Copper Flex H Size	1/0 AWG
Conductor - Copper Flex I Size	1/0 AWG
Conductor - Copper Flex K Size	1/0 AWG
Conductor - Copper Flex M Size	1/0 AWG
Conductor - Copper Str Navy Size	100 (61) Navy
Conductor - Copper Str Size	1/0
Conductor - CopperWeld Str Size	1/0 F AWG;1/0 G AWG;1/0 J AWG;1/0 K AWG
Conductor - CopperWeld Str Size Range	1/0 F AWG-1/0 K AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)