



YAV26L2NT14FX

by Burndy
Catalog ID: YAV26L2NT14FX

Prop 65 Notice

Flex Conductor Standard Barrel Narrow, 2/0 AWG 2/0 Weld 325/24, 1/4 in, 2.56 in L.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available.

Product Details

General

Application	For Flex Conductors
Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> • Chamfered • Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YAV-L-NTFX
UPC	781810285503

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.81 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - D inch	1.28 in
Dimension - Diameter Min Size inch	1.28 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.76 in
Dimension - Strip Length inch	13/16
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.34 in

Physical Attribute - Tongue Angle	Straight
-----------------------------------	----------

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	2/0 (375/#24)
Conductor - Copper DLO Size Range	2/0 (375/#24)
Conductor - Copper Flex G Size	2/0
Conductor - Copper Flex G Size Range	2/0
Conductor - Copper Flex H Size	2/0
Conductor - Copper Flex H Size Range	2/0
Conductor - Copper Flex I Size	2/0
Conductor - Copper Flex I Size Range	2/0
Conductor - Copper Flex K Size	2/0
Conductor - Copper Flex K Size Range	2/0
Conductor - Copper Flex M Size	2/0
Conductor - Copper Str Navy Size	125 (61)
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0
Conductor - CopperWeld Str Size	2/0 F;2/0 G;2/0 J;2/0 K;2/0 V

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
 47 East Industrial Park Drive
 Manchester, New Hampshire 03109

Customer Service Hours:
 8 AM - 8 PM Eastern Monday-Friday
 Emergency Service 24-hours/365 Days
 Phone: 1-800-346-4175
 1-603-647-5299 (International)