



YAV26LTC14FXB

by Burndy
Catalog ID: YAV26LTC14FXB

Prop 65 Notice

Uninsulated Copper compression lug, 1 Hole, 35kV, Tin plated, 5/16" Stud hole size

Product Details

General

Color Code	Black
Connector Type	Terminal
Feature - Barrel Style	Belled
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810310694
UPC 12 Digit	7818103106944

Dimensions

Dimension - B Length inch	0.81
Dimension - Bolt Hole Size inch	0.27
Dimension - Bolt Size fraction	5/16
Dimension - D inch	0.64 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7
Dimension - L Length Overall mm	49
Dimension - Length Overall inch	1.94 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.63 in

Dimension - Pad Width inch	0.93
Dimension - Thread Size	5/16
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kVA
Rating - Minimum Voltage	600
Voltage - Maximum	35000 V

Conductor Related

Conductor - Copper DLO Size	DLO (325/24)
Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)