



YAV28L53

by Burndy
Catalog ID: YAV28L53

Copper Tubing Hylug, 1/4, 2.275 in L, 1.120 in W, Tin plated.

Copper Tubing Hylug, 2.275 in L, 1.120 in W, Tin plated

Product Details

General

Application	For Copper AirCraft Cable
Connector Type	Terminal
Die Index	46
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Material Composition	<ul style="list-style-type: none"> DLP Copper Tin Plating
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810224861

Dimensions

Dimension - B Length fraction	7/8 in
Dimension - B Length inch	0.85 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size mm	7 mm
Dimension - Length Overall inch	2.28 in
Dimension - N inch	0.44 in
Dimension - Pad Width inch	1.12 in
Dimension - Stud Size inch	1/4 in
Dimension - Z inch	0.28 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Aircraft Size	AN-4/0
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)