



YAV2CL2BAG3

by Burndy
Catalog ID: YAV2CL2BAG3

Copper Compression Lug, Ring Tongue, 1 Hole w/ Inspection Hole, AN-2 Flex, 5/16" Stud, Short Barrel, Tin Plated

Product Details

General

Color Code	Orange
Connector Type	Terminal - Ring
Die Index	41
Feature - Barrel Style	- Chamfered - Skived
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	621945121911
UPC 12 Digit	621945121911

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.60 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - D inch	0.69 in
Dimension - Hole Size inch	0.33 in
Dimension - Hole Size mm	8 mm
Dimension - Inside Diameter inch	0.36 in
Dimension - L Length Overall mm	44 mm
Dimension - Length Overall inch	1.72 in
Dimension - N inch	0.34 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.69 in

Dimension - Strip Length inch	5/8
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.35 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	2 (150/#24)
Conductor - Copper Str Aircraft Size	AN 2
Conductor - Copper Str Aircraft Size Range	AN 2
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	10
Minimum Pack Quantity	3

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)