



YAV630FM12

by Burndy
Catalog ID: YAV630FM12

Non Insulated Cu Tubular Terminal, 1 Hole, 630 mm, M12 Stud, 4.34 IN L, Compression, 31 Index, 55 mm Strip Length

Product Details

General

Die Index	31
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	Metric Terminals
UPC	781810643013
UPC 12 Digit	7818106430133

Dimensions

Dimension - B Length inch	2.00 in
Dimension - L Length Overall mm	110 mm
Dimension - Length Overall inch	4.34 in
Dimension - Pad Width inch	2.69 in
Dimension - Strip Length inch	2.17 in
Dimension - Z inch	0.55 in

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size Range	N/A
-----------------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Standards - RoHS Compliance Status	CM

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)