



YAZ29TC38

by Burndy
Catalog ID: YAZ29TC38

Prop 65 Notice

Cu Tubing Hylug (One Hole Code), 1 Hole with Inspection Window, 250 kcmil Code, 250 Navy, 600V-35kV, 3/8" stud, Long, Compression, 0.40 in BCD, Yellow.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, With Inspection Window, Temperature Rating: 90 DEG C, Finish: Electro-Tin Plated, Tongue Angle: Straight, Wire Strip Length: 1-11/16 IN, Color Code: Yellow, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W29VT Die, (4), X29RT Die, (8), Hydraulic: BCT500HS, Y500CTHS Tool, W29VT, W29RT Die, (4), X29RT Die, (6), Y35, Y39, Y750, PAT750 Tool, U29RT Die, (2), Y46 Tool, U29RT Die With PUADP-1 Adapter, (2), Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11 Tool, (2), Die Index: 16

Product Details

General

Application	For Code Conductor
Color Code	Yellow
Connector Type	Terminal
Die Index	16
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Yes
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810240151
UPC 12 Digit	7818102401511

Dimensions

Dimension - B Length inch	1.62 in
Dimension - Bolt Hole Size inch	0.4 in
Dimension - Bolt Size fraction	3/8
Dimension - Hole Size inch	0.40 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	76 mm
Dimension - Length Overall inch	2.98 in
Dimension - N inch	0.41 in
Dimension - Outside Diameter inch	0.75 in

Dimension - Pad Width inch	1.10 in
Dimension - Strip Length inch	1-11/16
Dimension - Stud Size inch	3/8
Dimension - Z inch	0.42 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Navy Size	250 (61) Navy
Conductor - Copper Str Navy Size Range	250 (61) Navy
Conductor - Copper Str Size	250 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)