



## YAZ2C2TC1490

by Burndy  
Catalog ID: YAZ2C2TC1490

Prop 65 Notice

Cu Comp Terminal Code Cond, Bvl Entry, 2 Hole/W/InspWindow, #2 AWG Code, 60 Navy, 600 V-35 kV, 1/4" Stud, 0.62" Spacing, 90 Deg Bent, Lng bbl, Brown, 10 Index.

Two hole, Copper compression terminal code conductor, long barrel

## Product Details

### General

Application	For Flex Conductors
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Physical Attribute - Tongue Type	Standard
Plated	Yes
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive, Tin Plated
UPC	781810229262
UPC 12 Digit	7818102292622

### Dimensions

Dimension - B Length inch	1.25 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Height inch	1.74 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	40 mm
Dimension - Length Overall inch	1.58 in

Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.42 in
Dimension - Pad Width inch	0.60 in
Dimension - Strip Length inch	1-5/16
Dimension - Z inch	0.96 in
Physical Attribute - Tongue Angle	90 Degree

### Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

### Conductor Related

Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Navy Size Range	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - Material	Copper

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### For further technical assistance, please contact us

**BURNDY Headquarters**  
47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**  
8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)