



YAZ2CTC516

by Burndy
Catalog ID: YAZ2CTC516

Prop 65 Notice

Cu Tubing Hylug (One Hole Code), 1 Hole with Inspection Window, #2 AWG Code, 60 Navy, 600V-35kV, 5/16" stud, Long, Compression, 0.33 in BCD, Brown.

Features: With Inspection Window, Tongue Angle: Straight, Wire Strip Length: 1-5/16 IN, Color Code: Brown, Die Index: 10, Conductor Type: Copper, Finish: Electro-Tin Plated, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (2), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (2), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (2), Temperature Rating: 90 DEG C, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-3, MY29-11, MRC840 Tool, (2), Y1MRTC Tool, (4)

Product Details

General

| | |
|--------------------------------------|--------------------------------|
| Application | For Code Conductor |
| Color Code | Brown |
| Connector Type | Terminal |
| Die Index | 10 |
| Feature - Barrel Style | Skived |
| Feature - Barrel Type | Long |
| Material | Copper |
| Physical Attribute - Number of Holes | 1 |
| Plated | YES |
| Plating Type | Tin - Electro Plated |
| Sub Brand | HYLUG |
| Trade Name | HYLUG™ |
| Type | Long Barrel, Skive, Tin Plated |
| UPC | 781810243435 |
| UPC 12 Digit | 7818102434355 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length inch | 1.25 in |
| Dimension - Bolt Hole Size inch | 0.33 in |
| Dimension - Hole Size inch | 0.33 in |
| Dimension - Hole Size mm | 8 mm |
| Dimension - L Length Overall mm | 58 mm |
| Dimension - Length Overall inch | 2.27 in |
| Dimension - N inch | 0.34 in |
| Dimension - Outside Diameter inch | 0.42 in |

| | |
|-----------------------------------|----------|
| Dimension - Pad Width inch | 0.60 in |
| Dimension - Strip Length inch | 1-5/16 |
| Dimension - Z inch | 0.36 in |
| Physical Attribute - Tongue Angle | Straight |

Electrical Ratings

| | |
|--------------------------|-------|
| Rating - KVA | 35 kV |
| Rating - Minimum Voltage | 600 |
| Voltage - Maximum | 35000 |

Conductor Related

| | |
|----------------------------------|--------------|
| Conductor - Copper Str Navy Size | 60 (37) Navy |
| Conductor - Copper Str Size | 2 AWG |
| Conductor - Material | Copper |

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|----|
| Minimum Pack Quantity | 25 |
|-----------------------|----|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)