



YAZ342NTCFXB

by Burndy
Catalog ID: YAZ342NTCFXB

Prop 65 Notice

Cu compression long barrel flex conductor, 2 holes/W/ insp window, 373.3 kcmil(925/24), 350 kcmil nom, 1/2" stud, Blue, 19 index.

Features: Compression Belled End Terminal, With Inspection Window, Tongue Angle: Straight, Finish: Tin Plated, Wire Strip Length: 2-5/16 IN, Die Index: 9 or 470

Product Details

General

Application	For Flex Conductors
Connector Type	Terminal
Construction Material - Main	Copper
Feature - Barrel Style	- Belled - Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810238660
UPC 12 Digit	7818102386600

Dimensions

Dimension - B Length fraction	2-1/2 in
Dimension - B Length inch	2.48 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - Inside Diameter inch	0.83 in
Dimension - L Length Overall mm	159 mm
Dimension - Length Overall inch	6.27 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	1.24 in
Dimension - Pad Width inch	1.55 in
Dimension - Strip Length inch	3/8
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	373.7 (925/#24) DLO
Conductor - Copper DLO Size Range	373.7 (925/#24) DLO
Conductor - Copper Flex G Size	350 kcmil
Conductor - Copper Flex G Size Range	350 kcmil
Conductor - Copper Flex H Size	350 kcmil
Conductor - Copper Flex H Size Range	350 kcmil
Conductor - Copper Flex I Size	350 kcmil
Conductor - Copper Flex I Size Range	350 kcmil
Conductor - Copper Flex K Size	350 kcmil
Conductor - Copper Flex K Size Range	350 kcmil
Conductor - Copper Flex M Size	350 kcmil
Conductor - Copper Flex M Size Range	350 kcmil
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)