

# YAZV262TC14FX

by Burndy  
Catalog ID: YAZV262TC14FX

Prop 65 Notice

Cu Comp Terminal Flex Cond, 2 Hole/W/InspWindow, 2/0 Weld,2/0(325/#24)DLO Flex, 1/0 AWG Code, 600 V-35 kV, 1/4" Stud, 0.62" Spacing, Lng bbl, Black, 13 Index.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, With Inspection Window, Die Index: 13, Finish: Electro-Tin Plated, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Wire Strip Length: 1-9/16 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W26VT, W26RT, X26RT Die, (4), Hydraulic: BCT500HS, Y500CTHS Tool, W26VT, W26RT, X26RT Die, (4), Y35, Y39, Y750, PAT750 Tool, U26RT Die, (2), Y46 Tool, U26RT Die With PUADP-1 Adapter, (2), Color Code: Black, Dieless Tools (number Of Crimps): Y644HS Tool, (1), Y81KFT, Y81KFTMBH, PAT81KFT-18V, MY29-11 Tool, (2), Conductor Type: Flexible



## Product Details

### General

Application	For Flex Conductors
Color Code	Black
Connector Type	Terminal
Die Index	13
Feature - Barrel Style	<ul style="list-style-type: none"> <li>• Chamfered</li> <li>• Skived</li> </ul>
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810228449
UPC 12 Digit	7818102284499

### Dimensions

Dimension - B Length fraction	1-1/2 in
Dimension - B Length inch	1.50 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Bolt Size fraction	1/4
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	81 mm

Dimension - Length Overall inch	3.20 in
Dimension - Length Side B inch	3.20 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.63 in
Dimension - Pad Width inch	0.93 in
Dimension - Strip Length inch	1-9/16
Dimension - Z inch	0.34 in
Physical Attribute - Tongue Angle	Straight

## Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

## Conductor Related

Conductor - Copper DLO Size	2/0 (375/#24) DLO
Conductor - Copper DLO Size Range	2/0 (375/#24) DLO
Conductor - Copper Flex G Size	2/0 AWG
Conductor - Copper Flex G Size Range	2/0 AWG
Conductor - Copper Flex H Size	2/0 AWG
Conductor - Copper Flex H Size Range	2/0 AWG
Conductor - Copper Flex I Size	2/0 AWG
Conductor - Copper Flex I Size Range	2/0 AWG
Conductor - Copper Flex K Size	2/0 AWG
Conductor - Copper Flex K Size Range	2/0 AWG
Conductor - Copper Flex M Size	2/0 AWG
Conductor - Copper Flex M Size Range	2/0 AWG
Conductor - Copper Str Size	2/0 AWG
Conductor - CopperWeld Str Size	2/0 F AWG;2/0 G AWG;2/0 J AWG;2/0 K AWG;2/0 V AWG
Conductor - CopperWeld Str Size Range	2/0 F AWG-2/0 V AWG
Conductor - Material	Copper

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

**For further technical assistance, please contact us**

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)