



YAZV2CTC14FX

by Burndy
Catalog ID: YAZV2CTC14FX

Prop 65 Notice

Copper Compression Lug, 1 Hole w/ Inspection Window, 2 Flex, 1/4" Stud, Long Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available, With Inspection Window, Finish: Electro-Tin Plated, Tongue Angle: Straight, Temperature Rating: 90 DEG C, Die Index: 10, Wire Strip Length: 1-7/16 IN, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R Tool, W2CVT, W2CRT, X2CRT Die, (2), Hydraulic: BCT500HS, Y500CTHS Tool, W2CVT, W2CRT, X2CRT Die, (2), Y35, Y39, Y750, PAT750 Tool, U2CRT Die, (2), Y46 Tool, U2CRT Die With PUADP-1 Adapter, (2), Color Code: Brown, Dieless Tools (number Of Crimps): Y644HS, Y81KFT, Y81KFTMBH, PAT81KFT-18V Tool, (1), MY29-3, MY29-11, MRC840 Tool, (2), Y1MRTC Tool, (4), Conductor Type: Flexible

Product Details

General

Application	For Flex Conductors
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Skived
Feature - Barrel Type	Long
Material	Copper
Physical Attribute - Number of Holes	1
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Long Barrel, Skive
UPC	781810241257
UPC 12 Digit	7818102412577

Dimensions

Dimension - B Length fraction	1-3/8 in
Dimension - B Length inch	1.38 in
Dimension - Bolt Hole Size inch	0.27 in
Dimension - Hole Size inch	0.27 in
Dimension - Hole Size mm	7 mm
Dimension - L Length Overall mm	60 mm
Dimension - Length Overall inch	2.37 in
Dimension - N inch	0.31 in
Dimension - Outside Diameter inch	0.46 in

Dimension - Pad Width inch	0.68 in
Dimension - Strip Length inch	1-7/16
Dimension - Stud Size inch	1/4
Dimension - Z inch	0.33 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	3 (125/#24) DLO;2 (150/#24) DLO
Conductor - Copper DLO Size Range	3 (125/#24) DLO-2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex G Size Range	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex H Size Range	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex I Size Range	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex K Size Range	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Flex M Size Range	2 AWG
Conductor - Copper Str Size	2 AWG
Conductor - CopperWeld Str Size	2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG
Conductor - CopperWeld Str Size Range	2 A AWG-2 P AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)