



YBM25L2

by Burndy
Catalog ID: YBM25L2

Prop 65 Notice

One Piece Extruded Hylugs Copper Terminal, Ring Tongue, 1/0 AWG Flex Class I, 1/0(275/#24) DLO, 5/16" stud, 58 Index

Product Details

General

Connector Type	Terminal - Ring
Die Index	58
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Trade Name	HYLUG™
UPC	781810026212

Dimensions

Dimension - B Length fraction	11/16 in
Dimension - B Length inch	0.66 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Length Overall inch	1.56 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.67 in
Dimension - Pad Width inch	0.72 in
Dimension - Strip Length inch	3/4
Dimension - Stud Size inch	5/16
Dimension - Z inch	0.45 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper DLO Size	1/0 (275/#24)
Conductor - Copper Flex I Size	1/0
Conductor - Copper Str Aircraft Size	AN 1/0
Conductor - Copper Str Size	1/0
Conductor - Copper Str Size Range	1/0

Conductor Type	• CU C Solid-Size • CU C Str-Size
----------------	---

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)