



YBM26L1

by Burndy
Catalog ID: YBM26L1

Prop 65 Notice

Flag Type, Ring Tongue Electrolytic Cu Terminal, 2/0 AWG, 5/16" stud,
598 Index

Product Details

General

Connector Type	Terminal - Ring
Die Index	598
Feature - Barrel Style	Chamfered
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin - Electro Plated
Trade Name	HYLUG™
UPC	781810080726

Dimensions

Dimension - B Length fraction	13/16 in
Dimension - B Length inch	0.78 in
Dimension - Bolt Hole Size inch	0.33 in
Dimension - Bolt Size fraction	5/16
Dimension - Length Overall inch	1.65 in
Dimension - N inch	0.33 in
Dimension - Outside Diameter inch	0.76 in
Dimension - Pad Width inch	0.84 in
Dimension - Stud Size inch	5/16 in
Dimension - Z inch	0.45 in
Physical Attribute - Tongue Angle	90 Degree

Conductor Related

Conductor - Copper Str Aircraft Size	AN 2/0
Conductor - Copper Str Size	2/0
Conductor - Copper Str Size Range	2/0
Conductor Type	- CU C Solid-Size - CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	100
-----------------------	-----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)