



YC26A25

by Burndy
Catalog ID: YC26A25

Prop 65 Notice

Range-taking, C-shaped AL compression tap, Run: Aluminum: 1/0- 2/0, ACSR: 1/0-2/0, Tap: Aluminum: 1/0- 1/0, ACSR: 1/0-1/0

Product Details

General

Die Index	D
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810124529
UPC 12 Digit	7818101245299

Dimensions

Dimension - Height inch	1.38 in
Dimension - L Length Overall mm	65 mm
Dimension - Length Overall inch	2.56 in

Conductor Related

Conductor - ACSR Str Run Range	1/0 AWG - 2/0 AWG
Conductor - ACSR Str Tap Range	1/0 AWG - 1/0 AWG
Conductor - AL Str Run	1 AWG;1/0 AWG;2/0 AWG
Conductor - AL Str Run Range	1/0 AWG - 2/0 AWG
Conductor - AL Str Tap	1/0 AWG
Conductor - AL Str Tap Range	1/0 AWG - 1/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)