



## YC2A6

by Burndy  
Catalog ID: YC2A6

Prop 65 Notice

Al Compression Tap(C-Shaped),#2 Sol./Str.Al, #4 - #2 AWG ACSR(Run), #6 Sol./Str. Al(Tap), 1.50" L

## Product Details

### General

Die Index	C
Material	Aluminum
Plated	N
Plating Type	Unplated
Trade Name	CRIMPIT™
Type	YC-A, YC-U Series
UPC	781810122402
UPC 12 Digit	7818101224022

### Dimensions

Dimension - Height inch	1.00 in
Dimension - L Length Overall mm	38 mm
Dimension - Length Overall inch	1.50 in

### Conductor Related

Conductor - ACSR Str Run Range	4 AWG - 2 AWG
Conductor - AL Str Run Range	2 Sol. - 2 Str
Conductor - AL Str Tap Range	6 Sol. - 6 Str.

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)