



YC8L12TN

by Burndy
Catalog ID: YC8L12TN

Prop 65 Notice

Cu Thin Wall C-Tap, Compression, #8 - #10 AWG(Main), #10 - #12 AWG(Tap), 600 V, Tin Plated

Product Details

General

Color Code	Blue
Connector Type	C-Tap
Die Index	7
Material	Copper
Plated	Y
Plating Type	Tin - Electro Plated
Temperature Rating	194
Type	YC-L Series
UPC	781810243367
UPC 12 Digit	7818102433677

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - D inch	0.60 in
Dimension - Pad Width inch	0.21 in
Dimension - Strip Length inch	5/8

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 AWG-8 AWG
Conductor - Copper Str Tap	12 AWG;10 AWG
Conductor - Copper Str Tap Range	12 AWG-10 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	2000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)