



YC8L12

by Burndy
Catalog ID: YC8L12

Prop 65 Notice

Copper Compression C Tap, Thin Wall, 10 AWG (Run), 10 AWG (Tap).

Features: Manufactured Form High Conductivity Wrought Copper: Provides Low Resistance And Excellent Electrical Conductivity, Range-Taking Connector: Lowers Inventory Requirements, Reinforced Ribs: Provides Maximum Pull-Out Values, Compact Size: Easy To Tape And Insulate Connection, Economical: Provides Low Installed Cost, Use PUADP-1 Adapter With U Dies In Y46 HYPRESS, Color Code: Blue, Die Index: 7 Element A, Shape: C, Tools, Die Set Catalog Number, And (number Of Crimps): Mechanical: MD6, OUR840, MD7-34R, Y2MR Tool, W5CVT Die, (1), Wire Strip Length: 5/8 IN

Product Details

General

Application	For Making Copper Tap And Parallel Connections
Color Code	Blue
Connector Type	C-Tap
Die Index	7
Material	Copper
Physical Attribute - Number of Crimps Required	1
Plated	Y
Plating Type	Tin - Bright
Sub Brand	CRIMPIT
Temperature Rating	194
Type	YC-L Series
UPC	781810040119
UPC 12 Digit	7818100401199

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - D inch	0.60 in
Dimension - Pad Width inch	0.21 in
Dimension - Strip Length inch	5/8

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper Str Run	10 AWG;9 AWG;8 AWG
Conductor - Copper Str Run Range	10 AWG-8 AWG

Conductor - Copper Str Tap	12 AWG;10 AWG
Conductor - Copper Str Tap Range	12 AWG-10 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)