

YCA252NDTS

by Burndy
Catalog ID: YCA252NDTS

Prop 65 Notice

Cu Compression terminal Designed for terminating Cu Conductors to switch pads, 1/0 Str., 1/2 IN Stud, 2 Pad holes, Sealed oil tight and tin plated



Product Details

General

Connector Type	Terminal
Die Index	165
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin
Prefilled Oxide Inhibitor	N
Trade Name	HYLUG™
UPC	781810085080

Dimensions

Dimension - B Length fraction	1-4/7 in
Dimension - B Length inch	1.57 in
Dimension - D inch	2.67 in
Dimension - Hole Size fraction	5/9
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	136 mm
Dimension - Length Overall inch	5.34 in
Dimension - N inch	0.63 in
Dimension - Pad Width inch	0.91 in
Dimension - Z inch	0.30 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - Copper Str Size	1/0
-----------------------------	-----

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)