



YCA25R2N

by Burndy Catalog ID: YCA25R2N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equiptment taps to switch pads and other substation switch yard apparatus, 6.19 IN L.

 $\label{eq:Features:Aluminum compression HYLUG, NEMA standard mounting holes, Installed with same dies as equivalent full-tension sleeves$

Product Details

General

Application	Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.
Connector Type	Terminal
Die Index	243;BG;8A;KS18, 9A
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	Ν
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Туре	YCA-R-N
UPC	781810810460
UPC 12 Digit	7818108104600

Dimensions

Dimension - B Length inch	2.39 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	157 mm
Dimension - Length Overall inch	6.19 in
Dimension - Outside Diameter inch	0.62 in
Dimension - Pad Width inch	0.87 in

Conductor Related

Conductor - ACSR Str Size	1/0(.398) Awg (6-1 str)
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0(.373) Awg (7,19 str)
Conductor - AL Str Size Range	1/0 AWG

Certifications and Compliance

Certification - CSA	Approved
Certification COA	Approved

Certification - ETL	No	
Certification - UL Recognized	No	
Certification - cULus	No	
Standards - RoHS Compliance Status	СМ	
UL Listed	No	
Logistics		

1

Minimum Pack Quantity

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175 1-603-647-5299 (International)