



YCA25RL2N

by Burndy Catalog ID: YCA25RL2N

Prop 65 Notice

Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus, Die index: C, 247, 702

Product Details

General

Connector Type	Terminal
Die Index	247;702;C
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810422
UPC 12 Digit	7818108104222

Dimensions

Dimension - B Length inch	3.03 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	176 mm
Dimension - Length Overall inch	6.91 in
Dimension - Outside Diameter inch	0.80 in
Dimension - Pad Width inch	1.12 in

Conductor Related

Conductor - ACSR Cmpt Size Range	1/0 AWG
Conductor - ACSR Str Size	1/0 (6/1) Raven AWG
Conductor - ACSR Str Size Range	1/0 (6/1) Raven AWG
Conductor - AL Str Size	1/0 AWG
Conductor - AL Str Size Range	1/0 AWG
Conductor Type	ACSR C Str-Size AAC

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	СМ
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days Phone: 1-800-346-4175

1-603-647-5299 (International)