

YCA26RL2N

by Burndy
Catalog ID: YCA26RL2N

Prop 65 Notice

Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus,Die index:659



Product Details

General

Connector Type	Terminal
Die Index	659
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810446
UPC 12 Digit	7818108104466

Dimensions

Dimension - B Length inch	2.70 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	168 mm
Dimension - Length Overall inch	6.62 in
Dimension - Outside Diameter inch	0.83 in
Dimension - Pad Width inch	1.12 in

Conductor Related

Conductor - ACSR Cmpt Size Range	2/0 AWG
Conductor - ACSR Str Size	2/0 (6/1) Quail AWG
Conductor - ACSR Str Size Range	2/0 (6/1) Quail AWG
Conductor - AL Str Size	2/0 AWG
Conductor - AL Str Size Range	2/0 AWG
Conductor Type	• ACSR C Str-Size • AAC

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	25
-----------------------	----

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)