

YCA28R2N

by Burndy
Catalog ID: YCA28R2N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 6.83 IN L.

Features: Aluminum compression HYLUG , NEMA standard mounting holes, Installed with same dies as equivalent full-tension sleeves



Product Details

General

Application	Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.
Connector Type	Terminal
Die Index	249;11A;K-840
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Type	YCA-R-N
UPC	781810810477
UPC 12 Digit	7818108104777

Dimensions

Dimension - B Length inch	2.80 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	173 mm
Dimension - Length Overall inch	6.83 in
Dimension - Outside Diameter inch	0.88 in
Dimension - Pad Width inch	1.21 in

Conductor Related

Conductor - ACSR Str Size	4/0 (6/1) Penguin AWG
Conductor - ACSR Str Size Range	4/0 (6/1) Penguin AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)