

YCA2RL2N

by Burndy
Catalog ID: YCA2RL2N

Prop 65 Notice

Aluminum compression lug designed for terminating overhead conductors to switch pads and other substation switch yard apparatus,Die index: BG, 243, 687



Product Details

General

Connector Type	Terminal
Die Index	243;687;BG
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810408
UPC 12 Digit	7818108104088

Dimensions

Dimension - B Length inch	2.20 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	152 mm
Dimension - Length Overall inch	6 in
Dimension - Outside Diameter inch	0.66 in
Dimension - Pad Width inch	0.91 in

Conductor Related

Conductor - ACSR Cmpt Size Range	2 AWG
Conductor - ACSR Str Size	2 (6/1) Sparrow AWG;2 (7/1) Sparate AWG
Conductor - ACSR Str Size Range	2 (6/1) Sparrow AWG-2 (7/1) Sparate AWG
Conductor - AL Str Size	2 AWG
Conductor - AL Str Size Range	2 AWG
Conductor Type	• ACSR C Str-Size • AAC

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)