

YCA37R2N

by Burndy
Catalog ID: YCA37R2N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 8.15 IN L.

Features:Aluminum compression HYLUG , NEMA standard mounting holes,Installed with same dies as equivalent full-tension sleeves



Product Details

General

Application	Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.
Connector Type	Terminal
Die Index	261
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL
Trade Name	HYLUG™
Type	YCA-R-N
UPC	781810810705
UPC 12 Digit	7818108107055

Dimensions

Dimension - B Length inch	3.65 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	207 mm
Dimension - Length Overall inch	8.15 in
Dimension - Pad Width inch	1.94 in

Conductor Related

Conductor - ACSR Str Size	477 (24-7) kcmil; 477 (26-7) kcmil;477 (30-7) kcmil, 556.5 (18-1)
Conductor - ACSR Str Size Range	477 (24-7) kcmil; 477 (26-7) kcmil;477 (30-7) kcmil, 556.5 (18-1)
Conductor - AL Str Size	556 kcmil
Conductor - AL Str Size Range	556 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)