

YCA441A4N

by Burndy
Catalog ID: YCA441A4N

Prop 65 Notice

Aluminium Terminal, 4 Pad Holes, 1033.5 (37, 61) - 113 (61) kcmil Al., 575 Index



Product Details

General

Connector Type	Terminal
Die Index	575
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016770
UPC 12 Digit	7818100167700

Dimensions

Dimension - B Length inch	4.75 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	254 mm
Dimension - Length Overall inch	10 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - AL Str Size	1033.5 kcmil (37);1033.5 kcmil (61); 1113 kcmil (61)
Conductor - AL Str Size Range	1033.5 kcmil (37);1033.5 kcmil (61); 1113 kcmil (61)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)