

YCA451A4N

by Burndy
Catalog ID: YCA451A4N

Prop 65 Notice

Aluminium Terminal, 4 Pad Holes, 1113 (54-19) kcmil ACSR, 1272 (61) kcmil Al., 422 Index



Product Details

General

Connector Type	Terminal
Die Index	422
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810016725
UPC 12 Digit	7818100167255

Dimensions

Dimension - B Length inch	4.92 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	259 mm
Dimension - Length Overall inch	10.19 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	1113 (54-19) kcmil
Conductor - ACSR Str Size Range	1113 (54/19) kcmil
Conductor - AL Str Size	1272 (61) kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)