

YCA45R2N

by Burndy
Catalog ID: YCA45R2N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, Index: 352.

Features: Aluminum Compression Terminals



Product Details

General

Application	For AAC(STR,Compressed,compact), ACSR AND AAAC
Connector Type	Terminal
Die Index	352
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Trade Name	HYLUG™
Type	YCA-R-N
UPC	781810016701
UPC 12 Digit	7818100167011

Dimensions

Dimension - B Length inch	5.31 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	261 mm
Dimension - Length Overall inch	10.28 in
Dimension - Pad Width inch	2.55 in

Conductor Related

Conductor - ACSR Str Size	795 (54-7) kcmil;795 (26-/7) kcmil
Conductor - ACSR Str Size Range	795 (54-7) kcmil;795 (26-/7) kcmil
Conductor - AL Str Size	900 kcmil;954 kcmil;1000 kcmil
Conductor - AL Str Size Range	900 kcmil;954 kcmil;1000 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)