

YCAK28R4N

by Burndy
Catalog ID: YCAK28R4N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.36. IN L.

Features: Compression Terminal, Conductor Type: ACSR/6201/5005 (Compressed/Compact), Aluminum, Tools, Die Set Catalog Number, And (number Of Crimps): MD6, MD7 Tool, W249 Die, (6), Y35, Y750 Tool, U249 Die, (3), Y45 Tool, U249 Die With PT-6515 Adapter, (3), Y46 Tool, U249 Die With PUADP-1 Adapter, (3), Y48B Tool, C249 Die, (1), Y60BHU Tool, L249 Die, (2), Die Index: K840 Or 249 Or 11A



Product Details

General

Application	For ACSR/6201/5005 (Compressed/Compact), Aluminum
Die Index	249
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Trade Name	HYLUG™
Type	YCAK-R-N, Terminal
UPC	781810016749
UPC 12 Digit	7818100167499

Dimensions

Dimension - B Length inch	3.10 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	187 mm
Dimension - Length Overall inch	7.36 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	4/0 (6-1) AWG;4/0 (6-7) AWG
Conductor - ACSR Str Size Range	4/0 (6-1) AWG;4/0 (6-7) AWG
Conductor - AL Str Size	4/0 AWG
Conductor - AL Str Size Range	4/0 AWG

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)