

YCAK321R4N

by Burndy
Catalog ID: YCAK321R4N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.09 IN L.

Features:Aluminum compression HYLUG , NEMA standard mounting holes,Installed with same dies as equivalent full-tension sleeves



Product Details

General

Application	Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends.
Die Index	321
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	COMPRESSION TERMINAL, TERMINAL
Trade Name	HYLUG™
Type	YCAK-R-N
UPC	781810810255
UPC 12 Digit	7818108102555

Dimensions

Dimension - B Length inch	2.74 in
Dimension - Bolt Hole Size inch	0.56 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - L Length Overall mm	180 mm
Dimension - Length Overall inch	7.09 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size	336.4 (18-1) kcmil
Conductor - ACSR Str Size Range	336.4 (18-1) kcmil
Conductor - AL Str Size	336.4 kcmil;350 kcmil
Conductor - AL Str Size Range	336.4 kcmil;350 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No

Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)