



YCAK34A2G3

by Burndy
Catalog ID: YCAK34A2G3

Prop 65 Notice

Al Compression terminal, 500 kcmil 500 kcmil COMP, .56"stud, 6.55"L.

Features: Compression Terminal, Conductor Type: Copper, Aluminum Concentric And Compact, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U608, U786 Die, Y45 Tool, U608, U786 Die With PT-6515 Adapter, S786 Die, Y46 Tool, U608, U786 Die With PUADP-1 Adapter, P786 Die, Tongue Angle: Straight, Die Index: 608 Or 786

Product Details

General

| | |
|--|---|
| Application | For Copper, Aluminum Concentric And Compact |
| Die Index | 608;786 |
| Material | Aluminum |
| Physical Attribute - Pad Configuration | 2 Hole NEMA |
| Physical Attribute - Tongue Type | Standard |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | TERMINALS |
| Type | YCAK-A, Terminal |
| UPC | 781810810309 |
| UPC 12 Digit | 7818108103099 |

Dimensions

| | |
|-----------------------------------|----------|
| Dimension - B Length fraction | 6-1/2 in |
| Dimension - B Length inch | 2.19 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - L Length Overall mm | 165 mm |
| Dimension - Length Overall inch | 6.55 in |
| Dimension - Pad Width inch | 1.50 in |
| Physical Attribute - Tongue Angle | Straight |

Conductor Related

| | |
|-----------------------------------|-----------|
| Conductor - AL Str Size | 500 kcmil |
| Conductor - AL Str Size Range | 500 kcmil |
| Conductor - Copper Str Size | 500 kcmil |
| Conductor - Copper Str Size Range | 500 kcmil |

Certifications and Compliance

| | |
|------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |

| | |
|------------------------------------|----|
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)