

YCAK35R4N

by Burndy
Catalog ID: YCAK35R4N

Prop 65 Notice

AL compression lug designed for terminating jumper loop and equipment taps to switch pads and other substation switch yard apparatus, 7.34 IN L.

Features: Aluminum compression HYLUG , NEMA standard mounting holes, Installed with same dies as equivalent full-tension sleeves



Product Details

General

| | |
|--|--|
| Application | Used for terminating jumper loops and equipment taps at switchpads and other substation apparatus, or to YDW-R deadends. |
| Die Index | 317 |
| Material | Aluminum |
| Physical Attribute - Pad Configuration | 4 Hole NEMA |
| Plated | N |
| Plating Type | Unplated |
| Prefilled Oxide Inhibitor | Y |
| Sub Brand | COMPRESSION TERMINAL |
| Type | YCAK-R-N |
| UPC | 781810016756 |
| UPC 12 Digit | 7818100167566 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - B Length inch | 3.05 in |
| Dimension - Bolt Hole Size inch | 0.5 in |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - L Length Overall mm | 187 mm |
| Dimension - Length Overall inch | 7.34 in |
| Dimension - Pad Width inch | 3 in |

Conductor Related

| | |
|---------------------------------|--|
| Conductor - ACSR Str Size | 397.5 (26/7) Ibis kcmil; 397.5 (30/7) Larkspur kcmil |
| Conductor - ACSR Str Size Range | 397.5 kcmil (26-7,18-1,30-7 STR) |
| Conductor - AL Str Size | 397 kcmil |
| Conductor - AL Str Size Range | 397 kcmil |

Certifications and Compliance

| | |
|-------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |

| | |
|------------------------------------|----|
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)