



YCAK36A2G1

by Burndy
Catalog ID: YCAK36A2G1

Prop 65 Notice

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, 6.55 IN L

Product Details

General

Die Index	608;786
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Trade Name	HYLUG™
UPC	781810810323
UPC 12 Digit	7818108103233

Dimensions

Dimension - B Length fraction	6-1/2 in
Dimension - B Length inch	2.19 in
Dimension - D inch	3 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	165 mm
Dimension - Length Overall inch	6.55 in
Dimension - Pad Width inch	1.50 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	600 kcmil
Conductor - AL Str Size Range	600 kcmil

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No

Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	4
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)