



YCAK391A4N

by Burndy
Catalog ID: YCAK391A4N

Prop 65 Notice

Al Compression terminal, .56"stud, 9.88"L.

Features: Compression Terminal, Tools, Die Set Catalog Number, And (number Of Crimps): Y45 Tool, S342 Die, (6), Y46 Tool, P342 Die, (6), Y48B Tool, C342 Die, (3), Y60BHU Tool, L342 Die, (3), Conductor Type: Aluminum, Die Index: 342

Product Details

General

Application	For Aluminum
Die Index	342
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS
Type	YCAK, Terminal
UPC	781810810279
UPC 12 Digit	7818108102799

Dimensions

Dimension - B Length inch	5.25 in
Dimension - Bolt Hole Size inch	0.5 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	244 mm
Dimension - Length Overall inch	9.88 in
Dimension - Pad Width inch	3.00 in

Conductor Related

Conductor - AL Str Size Range	795 kcmil (37 STR),750 kcmil (61 STR)
-------------------------------	---------------------------------------

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)