



YCAK39A2G2

by Burndy
Catalog ID: YCAK39A2G2

Prop 65 Notice

AL compression lug for joining AL and CU cable to transformer and equipment pads, Prefilled with PENETROX, 6.96 IN L.

Features: Compression Terminal, Conductor Type: Aluminum Concentric And Compact, Tools, Die Set Catalog Number, And (number Of Crimps): Y35, Y750 Tool, U608, U786 Die, Y45 Tool, U608, U786 Die With PT-6515 Adapter, S786 Die, Y46 Tool, U608, U786 Die With PUADP-1 Adapter, P786 Die, Tongue Angle: Straight, Die Index: 608 Or 786

Product Details

General

Application	For Aluminum Concentric And Compact
Die Index	608;786
Material	Aluminum
Physical Attribute - Pad Configuration	2 Hole NEMA
Physical Attribute - Tongue Type	Standard
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	TERMINALS, HYLUG
Trade Name	HYLUG™
Type	YCAK-A, Terminal
UPC	781810810347
UPC 12 Digit	7818108103477

Dimensions

Dimension - B Length fraction	6-15/16 in
Dimension - B Length inch	2.50 in
Dimension - E Spacing between Holes fraction	1-3/4 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	176 mm
Dimension - Length Overall inch	6.96 in
Dimension - Pad Width inch	1.50 in
Physical Attribute - Tongue Angle	Straight

Conductor Related

Conductor - AL Str Size	750 kcmil
Conductor - AL Str Size Range	750 kcmil

Certifications and Compliance

Certification - CSA Approved	No
------------------------------	----

Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)