

YCAK43R4N

by Burndy
Catalog ID: YCAK43R4N

Prop 65 Notice

Aluminium Terminal, 4 Pad Holes, 605 (30-19), 636 (24-7, 26-7, 30-19), 666.6 (24-7) kcmil ACSR, 795 (37, 61), 700 (61), 750 (61) kcmil Al., 292 or 319 Index



Product Details

General

Die Index	292;319
Material	Aluminum
Physical Attribute - Pad Configuration	4 Hole NEMA
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
UPC	781810016787
UPC 12 Digit	7818100167877

Dimensions

Dimension - Bolt Hole Size inch	0.5 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	244 mm
Dimension - Length Overall inch	9.625 in
Dimension - Pad Width inch	3 in

Conductor Related

Conductor - ACSR Str Size Range	605 kcmil (30-19 STR),636 kcmil (24-7,26-7,30-19 STR),666.6 kcmil (24-7 STR)
Conductor - AL Str Size Range	795 kcmil (37,61 STR),700 kcmil (61 STR),750 kcmil (61 STR)

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	No

Logistics

Minimum Pack Quantity	2
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)